



HEADSET SN130

SN130

➤ SN130



Headset SN130 has been greatly used in language labs and computer labs all over word. It is famous for its good quality and good sound. These durable and professional headsets are specially designed to deliver the clearest sound quality in any environment.

It uses high quality skin for headband and ear cushions, which can be used under hot humid climate. Replaceable ear cushions on the headset allows for on-site replacement ensuring the headset will last for many years for everyday use.

Our headsets are available with various types of termination for any PC, laptop or tablets.

- **USB connection**
- **RJ11 modular connection**
- **3.5mm PC cable mini-jack connection**
- **3.5mm TRRS connection for tablets and ipads.**

➤ Advantages



➤ Specification


Loudspeaker diameter	50mm
Earphone sensibility	112 dB \pm 3dB
Impedance	32 Ω \pm 10%
Frequency range	20-20KHz
Output Power	20mv
Earpad	58mm opening
Microphone sensibility	-56db \pm 2db
Directivity	Omnidirectional
Cord Length	2.4 meters
Connector	2X3.5mm plug
volume control bar on cable	Yes
Gold plated cable	Yes
Weight	275g

Using Placing

- Language Learning Lab
- Computer Training lab
- Personal home using
- Conference
- Language Training Organizations

➤ Package

- ➔ **Bulk package:** We package 1 unit in one plastic bag, and 40 units in one carton. The size of carton is: 64*39*42CM, and the weight is about 15KG. We recommend our customers to choose bulk package, so that it can save a lot of air freight.



- ➔ **Retail package:** We package 2 units in one blank white package. The size of the package is: 18.5CM*14.5CM*20.5CM.



Warranty

- ① Two years limited warranty. Warranty will not apply if the product has been tampered with, disassembled or damaged by misuse, accident, modification or unauthorized repair. Since it is not easy for our oversea customers to send back the goods to us to maintain. We will send the problem components to our customers to replace. We will be responsible for all the cost within the warranty period.**
- ② If the products are overdue warranty period. We will send the problem components to our customers to replace, our customer need to be bear the freight and certain components cost if it needs.**
- ③ We provide 7*24 hours after-sales service. Customers can contact with us by Whatsapp, email, phone and so on.**